



# Technical Information IVS 535B

## IVS 535B Film Counter selectable between 3 and 4 perforation film transport

### 1. Introduction / Description

The IVS 535B (K2.47307.0 for PAL and K2.47306.0 for NTSC) has a film counter which is shown in the status line. This film counter can be set to footage. However, up to now this footage was based only on 4 perforation film advance. The action to be done is the change of an E-PROM. The update can be done by any ARRI Service Center or at ARRI Camera Service in Munich. During a regular service in a Service Center or in Munich, the customer will be charged for the E-PROM only. No additional charges for working time will apply.

### 2. Reason / Benefit

With the new software update, it is possible to select 3 perforation or 4 perforation film advance. This is a manual setting. In the sub menu STATUS there is a new line where you can select either 3 or 4 perforation film advance. The corresponding information is then displayed in the camera status line.

### 3. Serial Numbers affected

All IVS 535B PAL (K2.47307.0) with serial numbers lower than 2166 and NTSC (K2.47306.0) with a serial number lower than 2303.

ARRI Technical Info	Document Number	Ident Number	Name	Date	Page
535B-TI-001-IVS	1010-60-00-18-01	K5.58698.0	TFE / K. Jacumet	03.02.04	1 of 1