

ARRI Zoom Lenses & ARRI FSND Filters



CONFIGURATION OVERVIEW – 3.3.0 / 2018.01

© 2010 Arnold & Richter Cine Technik GmbH & Co. Betriebs KG. All rights reserved. This material is provided "as is" for information purposes only without any warranty. ARRI assumes no responsibility with regard to the performance or use of the products or typographical errors or inaccuracies of given information. Product specifications are subject to change without notice. For a full listing of all available components consult the price list.

ARRI Ultra Wide Zoom Lens

Format: SUPER 35 extended



Ultra Wide Zoom 9.5-18 mm
T2.9 | Ø 134 mm & 156 mm
K2.47620.0 (m), K2.0001686 (ft)

ARRI Anamorphic Ultra Wide Zoom Lens



Ultra Wide Zoom 19-36 mm
T4.2 | Ø 114 mm
K2.0006969 (m), K2.0006968 (ft)

ARRI/FUJINON ALURA Studio Zoom Lenses

Format: SUPER 35



ALURA ZOOM 18-80 mm
T2.6 | Ø 134 mm
K2.47930.0 (m), K2.47931.0 (ft)



ALURA ZOOM 45-250 mm
T2.6 | Ø 134 mm
K2.47932.0 (m), K2.47933.0 (ft)

ARRI/FUJINON ALURA LWZ Zoom Lenses

Format: SUPER 35




ALURA LWZ ZOOM 15.5-45 mm
T2.8 | Ø 114 mm
K2.47934.0 (m), K2.47935.0 (ft)



ALURA LWZ ZOOM 30-80 mm
T2.8 | Ø 114 mm
K2.47936.0 (m), K2.47937.0 (ft)

ARRI FSND Filters



Filters	Size	Ident Nr.	Filters	Size	Ident Nr.
ARRI FSND 0.3 Filter	6.6" x 6.6"	K2.0013892	ARRI FSND 0.3 Filter	4" x 5.65"	K2.0013887
ARRI FSND 0.6 Filter	6.6" x 6.6"	K2.0013894	ARRI FSND 0.6 Filter	4" x 5.65"	K2.0013901
ARRI FSND 0.9 Filter	6.6" x 6.6"	K2.0013896	ARRI FSND 0.9 Filter	4" x 5.65"	K2.0013895
ARRI FSND 1.2 Filter	6.6" x 6.6"	K2.0013898	ARRI FSND 1.2 Filter	4" x 5.65"	K2.0013904
ARRI FSND 1.5 Filter	6.6" x 6.6"	K2.0013900	ARRI FSND 1.5 Filter	4" x 5.65"	K2.0013897
ARRI FSND 1.8 Filter	6.6" x 6.6"	K2.0013902	ARRI FSND 1.8 Filter	4" x 5.65"	K2.0013890
ARRI FSND 2.1 Filter	6.6" x 6.6"	K2.0013905	ARRI FSND 2.1 Filter	4" x 5.65"	K2.0013903
ARRI FSND 2.4 Filter	6.6" x 6.6"	K2.0013906	ARRI FSND 2.4 Filter	4" x 5.65"	K2.0013891

ARRI/FUJINON LDS Extender



ALURA LDS Extender 1.4x (ALE1.4x)
K2.47926.0
ALURA LDS Extender 2.0x (ALE2.0x)
K2.47927.0

Alura Zoom	+	Alura Extender	=	Resulting combination
Alura 15.5-45 / T2.8	+	Alura LDS Extender 1.4x	=	Alura 22-63 / T4.0
Alura 15.5-45 / T2.8	+	Alura LDS Extender 2.0x	=	Alura 31-90 / T5.6
Alura 30-80 / T2.8	+	Alura LDS Extender 1.4x	=	Alura 42-112 / T4.0
Alura 30-80 / T2.8	+	Alura LDS Extender 2.0x	=	Alura 60-160 / T5.6
Alura 18-80 / T2.6	+	Alura LDS Extender 1.4x	=	Alura 25-112 / T3.7
Alura 18-80 / T2.6	+	Alura LDS Extender 2.0x	=	Alura 25-112 / T5.2
Alura 45-250 / T2.6	+	Alura LDS Extender 1.4x	=	Alura 63-350 / T3.7
Alura 45-250 / T2.6	+	Alura LDS Extender 2.0x	=	Alura 90-500 / T5.2