

CINE TAPE MEASURE Compatibility



CONFIGURATION OVERVIEW – 4.4.0 / 2013.09

© 2010 Arnold & Richter Cine Technik GmbH & Co. Betriebs KG. All rights reserved. This material is provided "as is" for information purposes only without any warranty. ARRI assumes no responsibility with regard to the performance or use of the products or typographical errors or inaccuracies of given information. Product specifications are subject to change without notice. For a full listing of all available components consult the price list.

Cine Tape Measure (CTM) Unit

by Cinematography Electronics
For more information please check
www.cinematographyelectronics.com



Cine Tape Measure Horn

Cable to Horn is included in CTM-Set



K-CAC-CTM
K2.52265.0

In CAC socket
of Camera

K-CCU-CTM
K2.52273.0

In CCU socket
of FEM-2

Cable ALEXA to Cinetape
KC 162-S ALEXA-CTM,
K2.0000464



KC-116-S, K2.65063.0
UMC-3 - CTM Cable



Videocameras Filmcameras



to
AUX socket
of UMC-3

LDD-FP-RDO
K2.54172.0



LDD-FP

Note: to connect the LDD-FP you need for
ARRICAM Studio: Studio Readout, K2.54008.0 for
ARRICAM Lite: Lite Frame Glow, K2.54037.0
or the Remote Control Station



Studio Lens
Data Box

Lite Lens
Data Box


FEM-2

Wireless Focus Tracking

LDD-FP-RDO
K2.54172.0



LDD-FP
with stored lens in
Lens Data Archive



UMC-3/3A

Wireless Focus Tracking

LC-Z1 / LC-Z2 / LC-M1 / LC-M2



WHA-3

WFU-3

CLM-2



WBU-3, WMU-3, WFU-3,
WEB-3, LDD-FP

LC-Z1 / LC-Z2 / LC-M1 / LC-M2



WHA-3

WFU-3

CLM-2



WBU-3, WMU-3, WFU-3,
WEB-3, LDD-FP

Note: Via the UMC-3/3A, any lens/camera combination can be used for focus tracking with the Cine Tape Measure, as long as the power source has 12-32 Volt and the lens is stored in the LENS DATA ARCHIVE. For cables and connections, please see the UMC-3 Configuration Overview. For LENS DATA ARCHIVE information please see the LDA Manual.